Low-lead union Y-strainer



128 series

Submittal Data 02168-25 NA — Issue Date 09/2025

Application

The 128 series Y-strainer is available with NPT male, sweat, press, PEX crimp and PEX expansion union connections. The union nut makes installation and maintenance fast, easy and efficient for a variety of tailpiece options. Constructed of DZR low-lead brass, 128 series Y-strainer is ideally suited for use in plumbing applications such as hot water recirculation systems and pairs up nicely with the Calefi 128 series FlowCal and FlowCal+ balancing valves. It also includes factory-installed PT ports to verify and certify flow rates where required. In addition, available separately, field-install Caleffi code 290030 full-port ball valve for isolation. The 128 series Y-strainers can also be used in hydronic systems.

Typical Specification

Furnish and install on the plans and described herein, a 128 series low-lead union Y-strainer as manufactured by Caleffi. Each Y-strainer must be designed with a y-body style including 1/2", 3/4", or 1" union sweat, NPT male threaded, press, PEX crimp and PEX expansion end connections. The design must include a DZR low-lead brass body and drain plug, with connections (<0.25% Lead content) certified by ICC-ES, stainless steel strainer with strainer mesh 0.87 mm (20 mesh), and peroxide-cured EPDM seals. Provided with two pressure/temperature test ports, Caleffi code 100001A. Provide with optional inlet and outlet isolation ball valves, code 290030, separately sourced, field installed. Each Y-strainer must be designed with flow Cv 7.0, 400 psi (28 bar) maximum working pressure and working temperature range of 32 to 212°F (0 to 100°C). Each Y-strainer shall be a Caleffi model 128 series or approved equal.

(See product instructions for specific installation information.)



Technical Data

Materials Valve

Body and drain plug: DZR low-lead brass Strainer: stainless steel Seals: peroxide-cured EPDM


NSF/ANSI/CAN 372, Drinking Water System Components-Lead Content Reduction of Lead in Drinking Water Act, California Health and Safety Code 116875 S.3874, Reduction in Drinking Water Act, certified by ICC-ES, file PMG-1360. PEX crimp fittings certified to ASTM F 1807. PEX expansion fittings certified to ASTM F 1960. US Patent: 7,246,635 B2.

Performance

Suitable Fluids: water, glycol solutions Max. percentage of glycol: 50% Max. working pressure: 400 psi (16 bar)
Working temperature range: 32 - 212°F (0–100°C)
Strainer mesh diameter: 0.97 mm (20 mesh)
Cv: 7.0
Connections:

Main inlet/outlet: 1/2", 3/4", 1" union sweat, NPT male, press,
PEX crimp or PEX expansion
Plugged blowdown port: 1/2" FNPT

Dimensions



Code	A (union connections)	В	С	D	Wt (lb/kg)
128741A 000	1/2" NPT male	6-11/16"			1.5/0.7
128742A 000	1/2" PEX expansion	8-13/16"			1.5/0.7
128744A 000	1/2" PEX crimp	7-13/16"			1.5/0.7
128746A 000	1/2" press*	6-9/16"			1.5/0.7
128749A 000	1/2" sweat	5-15/16"			1.3/0.6
128751A 000	3/4" NPT male	6-1/2"		2" 2-13/16"	1.5/0.7
128752A 000	3/4" PEX expansion	8-13/16"	2"		1.5/0.7
128754A 000	3/4" PEX crimp	7-13/16"	2 2-13/10	1.5/0.7	
128756A 000	3/4" press*	7-5/16"		2.1/0.95	
128759A 000	3/4" sweat	6-7/16"		2.1/0.95	
128761A 000	1" NPT male	7-3/16"		1.7/0.8	
128762A 000	1" PEX expansion	8-13/16"		1.7/0.8	
128764A 000	1" PEX crimp	8"			1.7/0.8
128766A 000	1" press*	7-1/4"			1.7/0.8
128769A 000	1" sweat	7-3/16"			2.2/1.0

*Lay length for press models:

-size 1/2 inch: 5"

-size 3/4 inch: 5-7/16"

-size 1 inch: 5-7/16"

We reserve the right to change our products and their relevant technical data	contained in this publication, at any time and wi	thout prior notice. Contractors should request pr	aduction drawings if profehricating the eyeter
vve reserve the right to change our products and their relevant technical date	contained in this publication, at any time and wi	itriout prior riotice. Contractors sriould request pr	oduction drawings if prefabilicating the system

	· · · · · · · · · · · · · · · · · · ·
Job name	Size
Job location	Quantity
Engineer	ΛΙ
Mechanical contractor	Comica
Contractor's P.O. No.	T N
Representative	Notes